

**LipuSmart-P-OB Basic stage**

**Product information for the product group**




**Item Technical Data 3558.36.00**

Nominal capacity	Nominal width	Contents			Key data			Weight	
		Sludge trap	Grease store	Overall	Type	P2	To	Empty	Full
		[l]	[l]	[l]		[kW]	[l]	[kg]	[kg]
NS 8.5	DN 150	940	475	1900	Pumpenset 4,0 kW	4	235	361	2261

ACO eServices on the Internet:



## Dimensions




Nominal capacity	Dimensions												
	L1	L2	L3	L4	L5	H1	H2	H3	H4	W1	W2	B3	D
	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
NS 8.5	2250	835	2777	300	680	1250	753	1880	1700	960	1130	1180	160

ACO eServices on the Internet:

Accessories

	Description	Used with	Description	Item number
	<p>Grease layer thickness measuring device</p>	<ul style="list-style-type: none"> <li>■ LipuJet-P                             <ul style="list-style-type: none"> <li>□ Oval NS 1 – 10</li> <li>□ Round NS 2 – 20</li> </ul> </li> <li>■ LipuJet-S                             <ul style="list-style-type: none"> <li>□ Oval NS 1 – 10</li> <li>□ Round NS 2 – 20</li> </ul> </li> <li>■ LipuSmart-P                             <ul style="list-style-type: none"> <li>□ Oval NS 1 – 10</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>■ For electronic measurement of layer of grease</li> <li>■ Suitable for liquid and/or congealing grease</li> <li>■ Measuring device with plug and used connecting cable, length: 3 m</li> <li>■ With two voltage-free changeover contacts to display full warning (80 %) and advance warning of fill level (50 %)</li> <li>■ With visual display of fill level</li> <li>■ With heated probe rod to increase reliability of operation</li> <li>■ Operating voltage: 230VAC/5 VA</li> <li>■ Max consumption approx. 12 W</li> <li>■ Weight: 2.8 kg</li> </ul>	<p><b>3300.11.50</b></p>
	<p>Grease layer thickness measuring device Multi Control</p>		<ul style="list-style-type: none"> <li>■ To determine the disposal intervals of grease separators</li> <li>■ Suitable for liquid and/or hardened fats</li> <li>■ Delineation with colour-touch-panel</li> <li>■ Continuous measure in percent</li> <li>■ With integrated SD-card (4GB) for recording of the measuring process</li> <li>■ With headed sounding stick (temperature is adjustable) to increase the operation safety</li> <li>■ Three free of potential contacts for output of pre-alarm (adjustable), full-alarm (adjustable) and error</li> <li>■ Measuring stick with adjusting scale</li> <li>■ Delineation with plug-in cable connection, 3 m</li> <li>■ Service voltage: 100 240VAC 50/60 Hz, 2 A</li> <li>■ Power: ca. 43 W</li> </ul>	
		<p>LipuJet-P LipuJet-S LipuSmart-P</p>	<p>Weight: 2.7 kg</p>	<p><b>3300.12.50</b></p>

	Description	Used with	Description	Item number
	Smell neutralisation		<ul style="list-style-type: none"> <li>■ Weight: 36.2 kg</li> </ul>	<b>7980.80.00</b>

You can find further accessories under → </35583600>

ACO eServices on the Internet:

Item number: 3558.36.00  
Version: 19.10.2018  
Page 4 of 4

Excluding errors and changes.

Infobox